


Cylinders



4414ME-3971

ME Cylinder Assembly

- Handed
- Cast iron
- Specify 24V or 120V
- Standard



4414ME-3071

ME Cylinder/Plate Assembly

- Handed
- "On/Off" switch assembly controls hold-open function
- Circuitry accepts either AC or DC input
- Please specify 24V or 120V
- Standard

Cover



4410ME-72MC

Metal Cover

- Handed

Arms



4410ME-3077

Regular Arm

- Non-handed
- 3-7/8" (98 mm) maximum reveal




4410ME-3077L

Long Arm

- For increasing opening to 180°
- 3-7/8" (98 mm) maximum reveal
- Optional

Switch



4410ME-3351 Switch Assembly


- Provides continuous hold-open function
- Available as 24V or 120V, please specify

Installation Accessories




4410ME-18 Mounting Plate

- Standard



4410ME-18G Mounting Plate

- Substituted for standard plate on flush ceiling installations
- Optional



4410ME - 3210 Transformer

- Reduces line voltage from 120V to 24V AC
- Mounted on cover for 4" (102 mm) x 4" x 2-1/8" (54 mm) junction box (by others)



4410ME-3354 ME Wiring Harness

- Three wire harness with 6" (152 mm) leads for field wiring connections